

Rubber Covered Neodymium

- Santoprene Rubber coating for scratch-free clamping
- Neodymium Magnets (NdFeB) inside for maximum holding forces
- Extremely good shear forces - high resistance to sliding
- Protects surfaces such as lacquered mild steel car body work
- Maximum recommended operating temperature is 60°C



Product Number	Height (mm)	Overall Height (I)	Overall Height (including bush length)	Bush Dia. (mm)	Thread Size (mm)	Colour	Coating	Dia. D (mm)	Holding Force (kg)
E851/1 EA781EE-66	6mm		0.45in	8mm	M4	Black	Santoprene Rubber	22mm	5
E851 EA781EE-61	6mm	0.5in	N/A	N/A	M4x6.5mm	Black	Santoprene Rubber	22mm	5
E853 EA781EE-62	6mm	0.8in	N/A	N/A	M6x15mm	Black	Santoprene Rubber	43mm	8.5
E853/1 EA781EE-67	6mm	N/A	0.4in	8mm	M4	Black	Santoprene Rubber	43mm	8.5
E854 EA781EE-63	8.5mm	0.9in	N/A	N/A	M8x15mm	Black	Santoprene Rubber	66mm	18
E854/1 EA781EE-68	8.5mm	N/A	0.6in	10mm	M5	Black	Santoprene Rubber	66mm	18
E855/1 EA781EE-69	8.5mm	N/A	0.65in	12mm	M8	Black	Santoprene Rubber	88mm	42
E855 EA781EE-64	8.5mm	0.9in	N/A	N/A	M8x15mm	Black	Santoprene Rubber	88mm	42