



Samarium Cobalt Shallow Pot Threaded

- 200° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body

Product Number	Height Body (mm)	Height (inc thread)	Thread Size (mm)	Ferrule Outer Dia.	Weight (kg)	Pull Force (kg)		Dia. D (mm)
E770 EA781EF-11	4.5	11.5	M3	6	0.0027	0.5		6
E771 EA781EF-12	4.5	11.5	M3	6	0.0036	1.1		8
E772 EA781EF-13	4.5	11.5	M3	6	0.0045	2		10
E773 EA781EF-14	4.5	11.5	M3	6	0.0075	4		13
E774 EA781EF-15	4.5	11.5	M4	8	0.009	6		16
E775 EA781EF-16	6	13	M4	8	0.0165	9		20
E776 EA781EF-17	7	14	M4	8	0.033	15		25
E777 EA781EF-18	7	15.5	M5	10	0.048	22		32