



Ferrite Shallow Pot-Threaded Hole

- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body
- Female thread

Product Number	Pot Height (mm)	Total Height	Thread Size (mm)	Weight (kg)	Pull Force (kg)	Units per Pack	Dia. D (mm)
E860 EA781EH-11	4.5	11	M3	0.003	0.4	20	10
E861 EA781EH-12	4.5	11.5	M3	0.005	1	20	13
E862 EA781EH-13	4.5	11.5	M3	0.006	1.8	20	16
E863 EA781EH-14	6	13	M3	0.011	3	10	20
E864 EA781EH-15	7	15	M4	0.022	4	10	25
E865 EA781EH-16	7	15	M4	0.032	8	5	32
E866 EA781EH-17	8	16	M4	0.045	10	5	36
E867 EA781EH-18	8	18	M5	0.06	12.5	5	40
E868 EA781EH-19	9	17	M4	0.09	18	1	47
E869 EA781EH-20	10	22	M6	0.11	22	1	50
E870 EA781EH-21	10.5	18.5	M4	0.145	28	1	57
E871 EA781EH-22	14	30	M8	0.24	35	1	63
E872 EA781EH-23	18	34	M10	0.52	60	1	80
E873 EA781EH-24	20	40	M10	0.82	70	1	90
E874 EA781EH-25	22	42	M12	0.94	90	1	100
E875 EA781EH-26	26	50	M14	1.72	130	1	125