



Ferrite Shallow Pot Magnets-Threaded hole

- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with red painted body
- Female thread

Product Number	Height (mm)	Thread	Thread Size (mm)	Weight (kg)	Pull Force (kg)	Units per Pack	Dia. D (mm)
E780 EA781EH-31	10	M8	M8	0.16	15	1	50
E781 EA781EH-32	18	M10	M10	0.56	55	1	80