



Ferrite Shallow Pot Magnets-Male Thread

- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body

Product Number	Pot Height (mm)	Total Height	Thread	Thread Size (mm)	Weight (kg)	Pull Force (kg)		Dia. D (mm)
E720 EA781EH-36	7	17	M5	M5	0.02	3.5		22
E723 EA781EH-37	7	22	M5	M5	0.032	8		32