



## Ferrite Shallow Pot Magnets (Zinc Plated)

- For press fitting applications
- 120° maximum operating temperature
- Excellent resistance to corrosion
- Mild steel pot with zinc plated body

Product Number	Height (mm)	Weight (kg)	Pull Force (kg)	Units per Pack	Dia. D (mm)
E700 EA781EH-1	4.5	0.002	0.4	20	10
E701 EA781EH-2	4.5	0.003	1	20	13
E702 EA781EH-3	4.5	0.0045	1.8	20	16
E703 EA781EH-4	6	0.01	3	10	20
E704 EA781EH-5	7	0.019	4	10	25
E705 EA781EH-6	7	0.03	8	10	32
E706 EA781EH-7	8	0.055	12.5	5	40
E707 EA781EH-8	10	0.1	22	5	50
E708 EA781EH-9	14	0.23	35	1	63
E709 EA781EH-10	18	0.485	60	1	80