



## Magnetic Tape

**Material:**

Strontium ferrite in thermo-plastic binder.  
 Max. operating temperature 80°C.

Magnetic on 1 face only.

Can be cut with scissors.

All supplied with standard acrylic adhesive.  
 FM652, FM663, FM664, FM665 are also available with premium acrylic or foam adhesive.

Product Number	Length (m)	Width (mm)	Thickness (mm)	Weight (kg)	Pull Force (g/cm <sup>2</sup> )	Units per Pack	Pull Force (oz/ft <sup>2</sup> )
EM884-R EA781EP-1	1	13	0.5	0.027	28	1	917
FM660 EA781EP-2	10	7.5	0.75	0.24	44	1	1441
FM661 EA781EP-3	10	12.5	0.75	0.39	44	1	1441
FM662 EA781EP-4	10	20	0.75	0.63	44	1	1441
FM652	30	10	1.5	1.7	55	1	1802
FM663 EA781EP-5	30	12.7	1.5	2.1	55	1	1802
FM664 EA781EP-6	30	20	1.5	3.3	55	1	1802
FM665 EA781EP-7	30	25.4	1.5	4.2	55	1	1802