

Mirage™

Full Coverage, Comfort, and Compliant Eye Protection

Dual Wraparound 9.75 Base Lens



Sleek, Lightweight Design

Offers a comfortable fit for both men and women

Polycarbonate Lens
Provides impact resistance



Dual Wraparound 9.75 Base Lens
Provides near perfect orbital seal

Optically Correct Lens
Distortion free

Displays



9522 - 36 Pair Display
9667 - Wall Mount

9523
12 Pair

9065
5 Pair

Meets ANSI Z87.1 Standards and Provides 99.9% UVA/UVB Protection.

Imprinting Available

Mirage™	
Part No.	Color
MR0110ID	Clear EA800AR-113
MR0120ID	Smoke EA800AR-114
MR0140ID	Amber
MR0160ID	Silver Mirror
MR0190ID	Indoor/Outdoor
MR01B0ID	Light Blue
MR01R0ID	Rainbow Mirror

Mirage™ Anti-Fog	
Part No.	Description
MR0111ID	Clear Anti-Fog
MR0120ID	Smoke Anti-Fog
MR0191ID	I/O Anti-Fog

Anti-Fog Lens Coating
Reduces Fogging

Packaging	
Unit	Qty
Box	12
Case	300

Mirage Family	
Mirage™ Small - 10% Smaller Frame	
Mirage™ RT - Rubber Tipped Temples	
Mirage™ USA - Assembled in the USA	
Mirage™ Foam	

Up to 2 colors:
Temple and/or Lens
(Right, Left, or Both)



RADIANS

Michigan

Toll Free: 800-483-2462
Phone: 616-866-2220 / Fax: 616-866-3615

Nevada

Toll Free: 877-723-9378
Phone: 775-284-8295 / Fax: 775-284-8291

Tennessee

Toll Free: 877-723-4267
Phone: 901-388-7776 / Fax: 901-266-2558