

EA815ZX-1~9
(電源トランス)

- 一次電圧 200V、220V
- 二次電圧 100V、110V
- 単相 複巻

番	容量	A	B	C	D	E	F	G	H	端子ネジ(mm)	絶縁種類	重量(kg)	形状
										一次/二次			
ZX-1	50VA	77	95	55	54	35	4.5X8	4	92	4	A	1.5	V
ZX-2	100VA	96	102	59	60	40	5.5X10	4	103	4	A	2.7	V
ZX-3	150VA	96	110	59	66	40	5.5X10	4	103	4	A	2.9	V
ZX-4	200VA	108	117	75	73	48	6X10	4	118	4	A	4.4	V
ZX-5	300VA	128	110	97	70	68	6.5X12	5	131	4	A	5.3	V
ZX-6	500VA	146	122	110	72	76	6.5X12	5	145	4	A	7	V
ZX-7	1kVA	146	180	110	122	76	6.5X12	5	145	4	A	12.2	V
ZX-8	1.5kVA	180	170	120	114		10X20		190	4	E	19	V
ZX-9	3kVA	200	190	138	144		10X20		220	5	B	30	V

(単位mm)

