



# TRANSFORMERS(複巻)FRシリーズ

BL型/ラグ端子式



SL型/ラグ端子式



24V type

形式	仕様					寸法 mm						重量 kg	取付穴 φ
	一次電圧	二次電圧	電流	形状	W	H	D	A	B	L			
EA815ZY-11	FR-639	0-100V	0-12V-24V	0.25A	BL	50	43	44	61		73	0.27	4.0×6.0
EA815ZY-12	FR-640			0.5A	BL	60	52	50	72		84	0.46	4.0×7.5
EA815ZY-13	FR-641			1.0A	BL	70	60	58	80		91	0.8	4.5×6.5
EA815ZY-14	FR-642			2.0A	BL	80	70	69	93		105	1.2	4.5×6.5
EA815ZY-15	FR-643			3.0A	SL	86	75	85	62	68		2.0	4.5×10
EA815ZY-16	FR-645			5.0A	SL	105	87	92	66	65		2.9	5.5×10