


TRANSFORMERS (複巻) FRシリーズ

BL型/ラグ端子式

SL型/ラグ端子式



12V type

形式	仕様					寸法 mm						重量 kg	取付穴 φ
	一次電圧	二次電圧	電流	形状	W	H	D	A	B	L			
EA815ZY-1	FR-519	0-100V	0-6V-12V	0.25A	BL	43	36	39	52		61	0.15	4.0×6.0
EA815ZY-2	FR-520			0.5A	BL	50	43	44	61		73	0.27	4.0×7.0
EA815ZY-3	FR-521			1.0A	BL	60	52	50	72		84	0.46	4.0×7.5
EA815ZY-4	FR-522			2.0A	BL	70	60	58	80		91	0.8	4.5×6.5
EA815ZY-5	FR-523			3.0A	BL	70	60	70	80		91	1.05	4.5×6.0
EA815ZY-6	FR-525			5.0A	SL	76	67	85	55	70			1.6