

# Small Diamond Discs on a Shank

Strauss diamond discs are designed for the fabrication, contouring, and shaping of metals and composites, available in the most popular shapes and in 3 grit sizes. The discs are mounted on a mandrel with an adaptor for Ø3 mm Shank, and will fit any Ø 2.35 or Ø 3 mm Rotary filing or polishing machine.

Individually packed and color coded for easy identification. Discs are available with double or single side diamond plating. Please contact us for further technical details.



Cat. No.	DD3/D350-210-017F	DD3/D350-210-022F	DD3/D350-220-017F	DD3/D350-220-022F	DD3/D355-190-017F
Size Ø (mm)	21	21	22	22	19
Grit	D54	D54	D54	D54	D54
Thickness (mm)	0.17	0.22	0.17	0.22	0.17
Sides	Double	Double	Double	Double	Double



Cat. No.	DD3/D355-190-010SF	DD3/D355-220-010SF	DD3/D355-220-016SF+C	DD3/D355-220-017SP/F	DD3/D355-220-019C	DD3/S356-220-010F	DD3/D358-220-019C	DD3/D358-220-019F
Size Ø (mm)	19	22	22	22	22	22	22	22
Grit	D30	D30	D30, D126	D54	D126	D54	D126	D54
Thickness (mm)	0.10	0.10	0.16	0.17	0.19	0.10	0.19	0.19
Sides	Double	Double	Double, top superfine, bottom coarse	Double	Double	Single	Double	Double

EA819DE-32 EA819DE-31



Cat. No.	DD3/D379-220-017F	DD3/D379-220-022F	DD3/D402-220-017F	DD3/D402-220-022F	DD3/S351-210-010F	DD3/D355-220-017F	DD3/S356-190-010F	DD3/S358-220-010C
Size Ø (mm)	22	22	22	22	21	22	19	22
Grit	D54	D54	D54	D54	D54	D54	D54	D126
Thickness (mm)	0.17	0.22	0.17	0.22	0.10	0.17	0.10	0.10
Sides	Double	Double	Double	Double	Single	Double	Single	Single

EA819DE-33

EA819DE-34