

EA819DJ-101~-108
CBNバ-

品番	刃径×刃長	角度	粒度	回転数
DJ-101	1.8×10mm	10°	#140	105000rpm
DJ-102	3.0×4.2mm	30°		
DJ-103	3.0×10mm	15°		
DJ-104	3.0×17mm	10°	#120	80000rpm
DJ-105	6.0×10mm	30°		
DJ-106	3.0×3.2mm	45°		
DJ-107	6.0×6.8mm			
DJ-108	10.0×11mm			

- 軸径…3.0mm
- 全長…50mm

