

6SUSSDP ステンレス用六角軸ドリル



コバルトハイス鋼を使用
ステンレスなどの難削材に最適

○1本入包装。

6SDSP 薄板用六角軸 すばっとドリル



食付性のよい薄板用六角軸ドリル
アクリル板にも良好

○1本入包装。

6SDSP 直径

単位:mm

	直径	溝長	全長	JANコード 4991893
EA824PJ-2.0	2.0	14	73	142273
EA824PJ-2.1	2.1	14	73	142280
EA824PJ-2.2	2.2	14	73	142297
EA824PJ-2.3	2.3	14	73	142303
EA824PJ-2.4	2.4	14	73	142310
	2.5	14	73	142327
	2.6	14	73	142334
EA824PJ-2.7	2.7	18	79	142341
EA824PJ-2.8	2.8	18	79	142358



直径	溝長	全長	JANコード 4991893	
2.9	18	79	142365	EA824PJ-2.9
3.0	18	79	142372	EA824PJ-3.0
3.1	18	79	142389	EA824PJ-3.1
3.2	18	79	142396	EA824PJ-3.2
3.3	18	79	142402	EA824PJ-3.3
3.4	20	82	142419	EA824PJ-3.4
3.5	20	82	142426	EA824PJ-3.5
3.6	20	82	142433	EA824PJ-3.6
3.7	20	82	142440	EA824PJ-3.7
3.8	22	82	142457	EA824PJ-3.8
3.9	22	82	142464	EA824PJ-3.9
4.0	22	82	142471	EA824PJ-4.0
4.1	22	82	142488	EA824PJ-4.1
4.2	22	82	142495	EA824PJ-4.2
4.3	24	88	142501	EA824PJ-4.3
4.4	24	88	142518	EA824PJ-4.4
4.5	24	88	142525	EA824PJ-4.5
4.6	24	88	142532	EA824PJ-4.6
4.7	24	88	142549	EA824PJ-4.7
4.8	26	92	142556	EA824PJ-4.8
4.9	26	92	142563	EA824PJ-4.9
5.0	26	92	142570	
5.2	26	92	142587	EA824PJ-5.2
5.5	28	95	142594	EA824PJ-5.5
6.0	28	95	142600	
6.5	35	95	142617	EA824PJ-6.5
7.0	35	95	142624	
7.5	35	95	142631	EA824PJ-7.5
8.0	35	95	142648	
8.5	35	95	142655	EA824PJ-8.5
9.0	35	95	142662	EA824PJ-9.0
9.5	35	95	142679	EA824PJ-9.5
10.0	35	95	142686	EA824PJ-10

食いつき性良好な
ローソク研ぎ

ガイド性が良好な
アングリア
(マージンなし)

●薄板でもバリがない

すばっとドリル

鉄工用ドリル

●狙った位置に真円に近い穴

すばっとドリル

鉄工用ドリル