

EA827HV-1～38

マシンリーマー



- 材質…MCO材(コバルト高速度鋼)
- 鋳鉄、鉄鋼一般の穴仕上げ加工に

(mm)					
品番	刃先径	シャンク径	刃長	全長	刃数
EA827HV-1	3	MT1	35	110	6枚
EA827HV-2	4				
EA827HV-3	5		45	120	
EA827HV-4	6		50	130	
EA827HV-5	7		55	140	
EA827HV-6	8		60	150	
EA827HV-7	9		70	160	
EA827HV-8	10				
EA827HV-9	11		75	170	
EA827HV-10	12				
廃番 EA827HV-11	13	MT2	80	180	8枚
EA827HV-12	14		85	190	
廃番 EA827HV-13	15		90	210	
EA827HV-14	16		95	215	
EA827HV-15	17		100	220	
EA827HV-16	18		105	225	
EA827HV-17	19		110	230	
EA827HV-18	20		120	240	
廃番 EA827HV-19	21				
廃番 EA827HV-20	22	MT3	130	250	10枚
廃番 EA827HV-21	23			270	
廃番 EA827HV-22	24				
廃番 EA827HV-23	25				
廃番 EA827HV-24	26				
EA827HV-25	27		140	280	
廃番 EA827HV-26	28				
EA827HV-27	29		150	290	
廃番 EA827HV-28	30				
廃番 EA827HV-29	31	MT4	160	300	
廃番 EA827HV-30	32			325	
廃番 EA827HV-31	33				
EA827HV-32	34				
EA827HV-33	35				
EA827HV-34	36				
EA827HV-35	37				
EA827HV-36	38		165	330	
廃番 EA827HV-37	39				
EA827HV-38	40				12枚