



コバルトスパイラルタップ

Cobalt Spiral Fluted Taps


HSCO




2.5P
食付き部




Type A



Type B



Type D



コバルトスパイラルタップ Cobalt Spiral Fluted Taps

呼び 並目	品番	形状 Type	精度	形状寸法							溝数	
				L	l	d	Ln	Dn	K	kL		
EA829ER-130	M3×0.5	CS030G	A	H2	46	18	4	-	-	3.2	6	3
EA829ER-140	M4×0.7	CS040I	B	H2	52	13	5	20	3.2	4	7	3
EA829ER-150	M5×0.8	CS050K	B	H2	60	16	5.5	24	4.05	4.5	7	3
EA829ER-160	M6×1.0	CS060M	B	H2	61	19	6	27	4.8	4.5	7	3
EA829ER-180	M8×1.25	CS080N	D	H2	70	22	6.2	30	5.9	5	8	3
EA829ER-210	M10×1.5	CS100O	D	H3	75	24	7	34	6.7	5.5	8	3
EA829ER-212	M10×1.25	CS100N	D	H2	75	24	7	34	6.7	5.5	8	3
	M12×1.75	CS120P	D	H2	82	29	8.5	41	8.2	6.5	9	3
	M12×1.5	CS120O	D	H2	82	29	8.5	39	8.2	6.5	9	3
	M12×1.25	CS120N	D	H2	80	29	8.5	39	8.2	6.5	9	3
	M14×2.0	CS140Q	D	H2	88	30	10.5	44	10.1	8	11	3
	M14×1.5	CS140O	D	H2	88	30	10.5	44	10.1	8	11	3
	M16×2.0	CS160Q	D	H2	95	32	12.5	47	12.1	10	13	3
	M16×1.5	CS160O	D	H2	95	32	12.5	47	12.1	10	13	3
	M18×2.5	CS180R	D	H3	100	37	14	52	13.5	11	14	3
	M18×1.5	CS180O	D	H3	95	37	14	52	13.5	11	14	3
	M20×2.5	CS200R	D	H3	105	37	15	54	14.5	12	15	3
	M20×1.5	CS200O	D	H3	95	37	15	52	14.5	12	15	3
	M22×2.5	CS220R	D	H3	115	38	17	55	16.5	13	16	4
	M22×1.5	CS220O	D	H3	95	38	17	53	16.5	13	16	4
	M24×3.0	CS240S	D	H3	120	45	19	62	18.5	15	18	4
	M24×1.5	CS240O	D	H3	95	38	19	53	18.5	15	18	4

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鋳鉄 FC	ダクタイル鋳鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	◎	◎			◎		○	○	○	