

ステンレス用スパイラルタップ

For Stainless Spiral Fluted Taps

HSSE

Ox




食付き部
2.5P



Type A



Type B



Type D



単位:mm

ステンレス用スパイラルタップ For Stainless Spiral Fluted Taps メートルねじ(Metric Thread)

単位:円(JPY)

呼び 並目	細目	品番	形状 Type	精度	形状寸法						溝数	定価	
					L	l	d	Ln	Dn	K			kφ
M2×0.4		HUS020E	A	H1	40	11	3	-	-	2.5	5	3	2,950
M2.3×0.4		HUS023E	A	H1	42	11	3	-	-	2.5	5	3	2,950
M2.6×0.45		HUS026F	A	H1	44	13	3	-	-	2.5	5	3	2,100
M3×0.5		HUS030G	A	H2	46	18	4	-	-	3.2	6	3	1,620
M4×0.7		HUS040I	B	H2	52	13	5	20	3.2	4	7	3	1,560
M5×0.8		HUS050K	B	H2	60	16	5.5	24	4.05	4.5	7	3	1,590
M6×1.0		HUS060M	B	H2	61	19	6	27	4.8	4.5	7	3	1,740
M8×1.25		HUS080N	D	H3	70	22	6.2	30	5.9	5	8	3	2,520
M8×1.0		HUS080M	D	H2	70	20	6.2	28	5.9	5	8	3	2,890
M10×1.5		HUS100O	D	H3	75	24	7	34	6.7	5.5	8	3	3,180
M10×1.25		HUS100N	D	H3	75	24	7	34	6.7	5.5	8	3	3,180
M10×1.0		HUS100M	D	H2	70	20	7	28	6.7	5.5	8	3	3,840
M12×1.75		HUS120P	D	H3	82	29	8.5	41	8.2	6.5	9	3	4,420
M12×1.5		HUS120O	D	H3	82	29	8.5	39	8.2	6.5	9	3	4,420
M12×1.25		HUS120N	D	H3	80	29	8.5	39	8.2	6.5	9	3	4,420
M12×1.0		HUS120M	D	H2	70	20	8.5	28	8.2	6.5	9	3	5,190
M14×2.0		HUS140Q	D	H3	88	30	10.5	44	10.1	8	11	3	6,020
M14×1.5		HUS140O	D	H3	88	30	10.5	44	10.1	8	11	3	6,020
M16×2.0		HUS160Q	D	H3	95	32	12.5	47	12.1	10	13	3	7,980
M16×1.5		HUS160O	D	H3	95	32	12.5	47	12.1	10	13	3	7,980

ステンレス用スパイラルタップ For Stainless Spiral Fluted Taps ウィットねじ(Whitworth Thread)

単位:円(JPY)

呼び 並目	細目	品番	形状 Type	精度	形状寸法						溝数	定価	
					L	l	d	Ln	Dn	K			kφ
1/4W20		HUSW07O	B	H2	61	19	6	27	5.2	4.5	7	3	2,160
5/16W18		HUSW09Q	D	H3	70	22	6.1	30	5.8	5	8	3	2,870
3/8W16		HUSW10R	D	H3	75	24	7	34	6.7	5.5	8	3	3,930
1/2W12		HUSW12U	D	H3	85	30	9	42	8.7	7	10	3	6,250
5/8W11		HUSW14W	D	H3	95	33	12	48	11.6	9	12	3	9,000
3/4W10		HUSW16X	D	H3	105	37	14	54	13.5	11	14	3	14,720

タップ・ダイス

EA829ER-330
EA829ER-340
EA829ER-350
EA829ER-360
EA829ER-380
EA829ER-410
EA829ER-412

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鋳鉄 FC	タタイル鋳鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	△	△			◎		△	△	○	