



# ステンレス用スパイラルタップ

For Stainless Spiral Fluted Taps

HSSE


Ox




2.5P  
食付き部




Type A



Type B



Type D



単位:mm

## ステンレス用スパイラルタップ For Stainless Spiral Fluted Taps メートルねじ(Metric Thread)

呼び 並目	品番	形状 Type	精度	形状寸法							溝数
				L	ℓ	d	Ln	Dn	K	kℓ	
M2×0.4	HUS020E	A	H1	40	11	3	-	-	2.5	5	3
M2.3×0.4	HUS023E	A	H1	42	11	3	-	-	2.5	5	3
M2.6×0.45	HUS026F	A	H1	44	13	3	-	-	2.5	5	3
M3×0.5	HUS030G	A	H2	46	18	4	-	-	3.2	6	3
M4×0.7	HUS040I	B	H2	52	13	5	20	3.2	4	7	3
M5×0.8	HUS050K	B	H2	60	16	5.5	24	4.05	4.5	7	3
M6×1.0	HUS060M	B	H2	61	19	6	27	4.8	4.5	7	3
M8×1.25	HUS080N	D	H3	70	22	6.2	30	5.9	5	8	3
M8×1.0	HUS080M	D	H2	70	20	6.2	28	5.9	5	8	3
M10×1.5	HUS100O	D	H3	75	24	7	34	6.7	5.5	8	3
M10×1.25	HUS100N	D	H3	75	24	7	34	6.7	5.5	8	3
M10×1.0	HUS100M	D	H2	70	20	7	28	6.7	5.5	8	3
M12×1.75	HUS120P	D	H3	82	29	8.5	41	8.2	6.5	9	3
M12×1.5	HUS120O	D	H3	82	29	8.5	39	8.2	6.5	9	3
M12×1.25	HUS120N	D	H3	80	29	8.5	39	8.2	6.5	9	3
M12×1.0	HUS120M	D	H2	70	20	8.5	28	8.2	6.5	9	3
M14×2.0	HUS140Q	D	H3	88	30	10.5	44	10.1	8	11	3
M14×1.5	HUS140O	D	H3	88	30	10.5	44	10.1	8	11	3
M16×2.0	HUS160Q	D	H3	95	32	12.5	47	12.1	10	13	3
M16×1.5	HUS160O	D	H3	95	32	12.5	47	12.1	10	13	3

## ステンレス用スパイラルタップ For Stainless Spiral Fluted Taps ウィットねじ(Whitworth Thread)

呼び 並目	品番	形状 Type	精度	形状寸法							溝数
				L	ℓ	d	Ln	Dn	K	kℓ	
1/4W20	HUSW070	B	H2	61	19	6	27	5.2	4.5	7	3
5/16W18	HUSW09Q	D	H3	70	22	6.1	30	5.8	5	8	3
3/8W16	HUSW10R	D	H3	75	24	7	34	6.7	5.5	8	3
1/2W12	HUSW12U	D	H3	85	30	9	42	8.7	7	10	3
5/8W11	HUSW14W	D	H3	95	33	12	48	11.6	9	12	3
3/4W10	HUSW16X	D	H3	105	37	14	54	13.5	11	14	3

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鋳鉄 FC	ダクタイル鋳鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	△	△			◎		△	△	○	