



コバルトジェットタップ(ポイントタップ)【通り穴用】

Cobalt Jet Screw Taps(Point Taps) For Through Holes


HSCO




4P
食付き部




Type A



Type B



Type D



単位:mm

コバルトジェットタップ(通り穴用) Cobalt Jet Screw Taps(For Through Holes)

呼び 並目	品番	形状 Type	精度	形状寸法							溝数
				L	ℓ	d	Ln	Dn	K	kℓ	
M3×0.5	CJ030G	A	H2	46	18	4	-	-	3.2	6	3
M4×0.7	CJ040I	B	H2	52	13	5	20	3.2	4	7	3
M5×0.8	CJ050K	B	H3	60	16	5.5	24	4.05	4.5	7	3
M6×1.0	CJ060M	B	H3	61	19	6	27	4.8	4.5	7	3
M8×1.25	CJ080N	D	H3	70	22	6.2	30	5.9	5	8	3
M10×1.5	CJ100O	D	H3	75	24	7	34	6.7	5.5	8	3
M10×1.25	CJ100N	D	H3	75	24	7	34	6.7	5.5	8	3
M12×1.75	CJ120P	D	H3	82	29	8.5	41	8.2	6.5	9	3
M12×1.5	CJ120O	D	H3	82	29	8.5	39	8.2	6.5	9	3
M12×1.25	CJ120N	D	H3	80	29	8.5	39	8.2	6.5	9	3
M14×2.0	CJ140Q	D	H4	88	30	10.5	44	10.1	8	11	3
M14×1.5	CJ140O	D	H3	88	30	10.5	44	10.1	8	11	3
M16×2.0	CJ160Q	D	H4	95	32	12.5	47	12.1	10	13	3
M16×1.5	CJ160O	D	H3	95	32	12.5	47	12.1	10	13	3
M18×2.5	CJ180R	D	H4	100	37	14	52	13.5	11	14	3
M18×1.5	CJ180O	D	H4	95	37	14	52	13.5	11	14	3
M20×2.5	CJ200R	D	H4	105	37	15	54	14.5	12	15	3
M20×1.5	CJ200O	D	H4	95	37	15	52	14.5	12	15	3
M22×2.5	CJ220R	D	H4	115	38	17	55	16.5	13	16	4
M22×1.5	CJ220O	D	H4	95	38	17	53	16.5	13	16	4
M24×3.0	CJ240S	D	H4	120	45	19	62	18.5	15	18	4
M24×1.5	CJ240O	D	H4	95	38	19	53	18.5	15	18	4

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鉄 FC	ダクタイル鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	◎	◎			◎		○	○	○	