


コバルトジェットタップ(ポイントタップ) 通り穴用

Cobalt Jet Screw Taps(Point Taps) For Through Holes

HSCO



食付き部
4P



単位:mm

タップ・ダイス

EA829EV-130
EA829EV-140
EA829EV-150
EA829EV-160
EA829EV-180
EA829EV-210
EA829EV-212

コバルトジェットタップ(通り穴用) Cobalt Jet Screw Taps(For Through Holes) 単位:円(JPY)

呼び 並目	呼び 細目	品番	形状 Type	精度	形状寸法							溝数	定価
					L	l	d	Ln	Dn	K	kl		
M3×0.5		CJ030G	A	H2	46	18	4	-	-	3.2	6	3	2,050
M4×0.7		CJ040I	B	H2	52	13	5	20	3.2	4	7	3	1,950
M5×0.8		CJ050K	B	H3	60	16	5.5	24	4.05	4.5	7	3	1,980
M6×1.0		CJ060M	B	H3	61	19	6	27	4.8	4.5	7	3	2,130
M8×1.25		CJ080N	D	H3	70	22	6.2	30	5.9	5	8	3	3,130
M10×1.5		CJ100O	D	H3	75	24	7	34	6.7	5.5	8	3	3,920
M10×1.25		CJ100N	D	H3	75	24	7	34	6.7	5.5	8	3	3,920
M12×1.75		CJ120P	D	H3	82	29	8.5	41	8.2	6.5	9	3	5,460
M12×1.5		CJ120O	D	H3	82	29	8.5	39	8.2	6.5	9	3	5,460
M12×1.25		CJ120N	D	H3	80	29	8.5	39	8.2	6.5	9	3	5,460
M14×2.0		CJ140Q	D	H4	88	30	10.5	44	10.1	8	11	3	7,530
M14×1.5		CJ140O	D	H3	88	30	10.5	44	10.1	8	11	3	7,530
M16×2.0		CJ160Q	D	H4	95	32	12.5	47	12.1	10	13	3	9,990
M16×1.5		CJ160O	D	H3	95	32	12.5	47	12.1	10	13	3	9,990
M18×2.5		CJ180R	D	H4	100	37	14	52	13.5	11	14	3	13,710
M18×1.5		CJ180O	D	H4	95	37	14	52	13.5	11	14	3	13,710
M20×2.5		CJ200R	D	H4	105	37	15	54	14.5	12	15	3	17,670
M20×1.5		CJ200O	D	H4	95	37	15	52	14.5	12	15	3	17,670
M22×2.5		CJ220R	D	H4	115	38	17	55	16.5	13	16	4	22,940
M22×1.5		CJ220O	D	H4	95	38	17	53	16.5	13	16	4	22,940
M24×3.0		CJ240S	D	H4	120	45	19	62	18.5	15	18	4	28,660
M24×1.5		CJ240O	D	H4	95	38	19	53	18.5	15	18	4	28,660

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鋳鉄 FC	タタイル鋳鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	◎	◎			◎		○	○	○	