




# ステンレス用ジェットタップ(ポイントタップ) 通り穴用

For Stainless Jet Screw Taps (Point Taps) For Through Holes

HSSE Ox 通り穴用 食付き部 4P



## ステンレス用ジェットタップ (通り穴用) For Stainless Jet Screw Taps (For Through Holes)

呼び 並目	品番	形状 Type	精度	形状寸法							溝数
				L	l	d	ln	Dn	K	kL	
M2×0.4	HUJ020E	A	H1	40	11	3	-	-	2.5	5	3
M2.3×0.4	HUJ023E	A	H1	42	11	3	-	-	2.5	5	3
M2.6×0.45	HUJ026F	A	H2	44	13	3	-	-	2.5	5	3
M3×0.5	HUJ030G	A	H2	46	18	4	-	-	3.2	6	3
M4×0.7	HUJ040I	B	H2	52	13	5	20	3.2	4	7	3
M5×0.8	HUJ050K	B	H3	60	16	5.5	24	4.05	4.5	7	3
M6×1.0	HUJ060M	B	H3	61	19	6	27	4.8	4.5	7	3
M8×1.25	HUJ080N	D	H3	70	22	6.2	30	5.9	5	8	3
M8×1.0	HUJ080M	D	H3	70	20	6.2	28	5.9	5	8	3
M10×1.5	HUJ100O	D	H3	75	24	7	34	6.7	5.5	8	3
M10×1.25	HUJ100N	D	H3	75	24	7	34	6.7	5.5	8	3
M10×1.0	HUJ100M	D	H3	70	20	7	30	6.7	5.5	8	3
M12×1.75	HUJ120P	D	H3	82	29	8.5	41	8.2	6.5	9	3
M12×1.5	HUJ120O	D	H3	82	29	8.5	39	8.2	6.5	9	3
M12×1.25	HUJ120N	D	H3	80	29	8.5	39	8.2	6.5	9	3
M12×1.0	HUJ120M	D	H3	70	20	8.5	28	8.2	6.5	9	3
M14×2.0	HUJ140Q	D	H4	88	30	10.5	44	10.1	8	11	3
M14×1.5	HUJ140O	D	H3	88	30	10.5	44	10.1	8	11	3
M16×2.0	HUJ160Q	D	H4	95	32	12.5	47	12.1	10	13	3
M16×1.5	HUJ160O	D	H3	95	32	12.5	47	12.1	10	13	3

推奨被削材	構造用鋼 SS400	低炭素鋼 S15C	高炭素鋼 S55C	合金鋼 SCM	調質鋼 HRC25~35	調質鋼 HRC35~40	ステンレス SUS	鋳鉄 FC	ダクタイル鋳鉄 FCD	アルミニウム合金 AL	銅合金 Cu	チタン合金 Ti
	△	△	△	△			◎		△	△	○	