

電動油圧パンチャ



品番	穴あけ能力				
	軟鋼板 (SS400)		ステンレス (SUS304)		
	丸穴	長穴	丸穴		
EA858HD	14 (板厚6)	11 × 16.5 (板厚6)	14 (板厚5)		
EA858HE	19 (板厚6)	14 × 21 (板厚6)	18 (板厚5)		
	電源	電流	消費電力	重量	サイズ
HD	AC100V	10.5A	1010W	10kg	178 × 37.5 × 418mm
HE		11.0A	1050W	13.9kg	195 × 55 × 484mm

コード...2心・2.5m

付属品...

スチールケース、プラスドライバ、ポンチ11mm(本体装着)、マイナドライバ、Bダイス11mm(本体装着)、スパナ(10 × 13mm)、スタンドベース(本体装着)、スパナ(17 × 19mm)、工具箱、六角棒スパナ(M4ねじ用)、油さし(油圧オイル)、六角棒スパナ(M5ねじ用)、サイドハンドル、六角棒スパナ(M6ねじ用)、六角棒スパナ(M8ねじ用)

ポンチ & ダイス(丸穴)



ポンチ(丸穴用)

品番	穴径 (mm)	板厚 (mm)	仕様
EA858HD-1	3.4	1.6	HD用
EA858HD-2	4.2	2.3	
EA858HD-3	5		
EA858HD-4	5.5		
EA858HD-5	6		
EA858HD-6	6.5		
EA858HD-7	8		
EA858HD-8	8.5		
EA858HD-9	10		
EA858HD-10	11		
EA858HD-11	12		
EA858HD-12	13		
EA858HD-13	14		
EA858HD-14	15		
EA858HD-15	16		
EA858HD-16	17		
EA858HD-17	18		
EA858HD-18	18.5		
EA858HD-19	19	HE用	

ダイス(丸穴薄板)HD用

品番	穴径 (mm)	板厚 (mm)	仕様
EA858HD-1D	3.4	1.6	HD用
EA858HD-2D	4.2	2.3	
EA858HD-3D	5	3.2	
EA858HD-4D	5.5		
EA858HD-5D	6		
EA858HD-6D	6.5		
EA858HD-7D	8		
EA858HD-8D	8.5		
EA858HD-9D	10		
EA858HD-10D	11		
EA858HD-11D	12		
EA858HD-12D	13		
EA858HD-13D	14		

ダイス(丸穴薄板)HE用

品番	穴径 (mm)	板厚 (mm)	仕様
EA858HE-1D	6	3.2	HE用
EA858HE-2D	6.5		
EA858HE-3D	8		
EA858HE-4D	8.5		
EA858HE-5D	10		
EA858HE-6D	11		
EA858HE-7D	12		
EA858HE-8D	13		
EA858HE-9D	14		
EA858HE-10D	15		
EA858HE-11D	18		
EA858HE-12D	19		

ダイス(丸穴厚板)HD用

品番	穴径 (mm)	板厚 (mm)	仕様
EA858HD-16D	5.5	4.5	HD用
EA858HD-17D	6	6.0	
EA858HD-18D	6.5		
EA858HD-19D	8		
EA858HD-20D	8.5		
EA858HD-21D	10		
EA858HD-22D	11		
EA858HD-23D	12		
EA858HD-24D	13		
EA858HD-25D	14		

ダイス(丸穴厚板)HE用

品番	穴径 (mm)	板厚 (mm)	仕様
EA858HE-16D	6	4.5	HE用
EA858HE-17D	6.5	6	
EA858HE-18D	8		
EA858HE-19D	8.5		
EA858HE-20D	10		
EA858HE-21D	11		
EA858HE-22D	12		
EA858HE-23D	13		
EA858HE-24D	14		
EA858HE-25D	15		
EA858HE-26D	16		
EA858HE-27D	17		
EA858HE-28D	18		
EA858HE-29D	18.5		
EA858HE-30D	19		

ポンチ & ダイス(長穴)



ポンチ(長穴用)

品番	穴径(mm)	板厚(mm)	仕様
EA858HE-1	8.5 × 17	3.2	HE用
EA858HE-2	9.0 × 18		
EA858HE-3	10 × 20		
EA858HE-4	12 × 18		
EA858HE-5	14 × 21		
EA858HE-6	6.5 × 10		HD・HE用
EA858HE-7	6.5 × 13		
EA858HE-8	8.5 × 13		
EA858HE-9	9 × 13.5		
EA858HE-10	10 × 15		
EA858HE-11	11 × 16.5		

ダイス(長穴薄板)HD用

品番	穴径(mm)	板厚(mm)	仕様
EA858HD-26D	6.5 × 10	3.2	HD用
EA858HD-27D	8.5 × 13		
EA858HD-28D	11 × 16.5		

ダイス(長穴厚板)HD用

品番	穴径(mm)	板厚(mm)	仕様
EA858HD-31D	6.5 × 10	6.0	HD用
EA858HD-32D	6.5 × 13		
EA858HD-33D	8.5 × 13		
EA858HD-34D	9.0 × 13.5		
EA858HD-35D	10 × 15		
EA858HD-36D	11 × 16.5		

ダイス(長穴薄板)HE用

品番	穴径(mm)	板厚(mm)	仕様
EA858HE-31D	6.5 × 13	3.2	HE用
EA858HE-32D	8.5 × 13		
EA858HE-33D	11 × 16.5		
EA858HE-34D	8.5 × 17		
EA858HE-35D	9 × 18		
EA858HE-36D	10 × 20		
EA858HE-37D	12 × 18		

ダイス(長穴厚板)HE用

品番	穴径(mm)	板厚(mm)	仕様
EA858HE-41D	6.5 × 10	6	HE用
EA858HE-42D	6.5 × 13		
EA858HE-43D	8.5 × 13		
EA858HE-44D	9 × 13.5		
EA858HE-45D	10 × 15		
EA858HE-46D	11 × 16.5		
EA858HE-47D	8.5 × 17		
EA858HE-48D	9 × 18		
EA858HE-49D	10 × 20		
EA858HE-50D	12 × 18		
EA858HE-51D	14 × 21		