

ダイヤモンドコアドリル(替刃のみ) (EA865C・CA用)
EA865CB-25~160



品番	刃先径 (mm)	有効長	カッター 長	チップ厚	重量 (g)
EA865CB-25	25mm	150mm	180mm	3.8mm	179.7
EA865CB-29	29				171.0
EA865CB-32	32				193.0
EA865CB-35	35				203.5
EA865CB-38	38				231.2
EA865CB-45	45				286.2
EA865CB-50	50				215.1
EA865CB-55	55				249.7
EA865CB-60	60				282.9
EA865CB-65	65				294.0
EA865CB-70	70				297.7
EA865CB-75	75				327.4
EA865CB-80	80				376.9
EA865CB-90	90				467.9
EA865CB-95	95				546.0
EA865CB-100	100				549.0
EA865CB-105	105				633.8
EA865CB-110	110				634.7
EA865CB-120	120				743.5
EA865CB-130	130				834.1
EA865CB-150	150	1000.0			
EA865CB-160	160	1120.4			

取扱い中止

取扱い中止
 取扱い中止

替センターピン (EA865C・CA用)
EA865CB-1



- 全長…228mm
- 重量…138g
- φ25～φ220用