

6' & 8'

3-IN-1 LADDER

A-FRAME - EXTENSION - LEANING

1. ONE-HANDED GRIP-N-GO™ HINGE

One-handed Grip-N-Go hinge operation allows for a quick and seamless transition between stepladder, extension and leaning ladder configurations.

2. ROTATING WALL PAD

Get closer to your work with the rotating wall pad. In the leaning position, it conforms to inside and outside corners, walls, poles and 2x4 studs.

3. NON-CONDUCTIVE, HI-VIZ GREEN FIBERGLASS

Increases ladder visibility. Usable on job sites that require fiberglass ladders.

4. V-BAR

Non-marring V-bar on the extension side of the ladder allows you to lean your ladder on outside corners, walls, studs and poles while in extension configuration.

5. FUNCTIONAL REAR SECTION

Allows access to tight workspaces between wall studs, ceiling trusses and roof or attic access ports.

6. GROUND CUE®

Makes an audible click when you have reached the final step of your descent.

7. SURE-SET™ SPIKE FEET

Adds extra stability on job sites and can be used in either the pad or spike foot position.



NON-CONDUCTIVE FIBERGLASS
FIBRA DE VIDRIO NO CONDUCTORA





Inside Corner Rotating Wall Pad



One-Handed Grip-N-Go Hinge



V-Bar on Outside Corner



Outside Corner Rotating Wall Pad



Attic Access



Sure-Set Foot in Spike Position



V-Bar on Pole

PRODUCT DESCRIPTION

The King Kombo Technical brings even more versatility to the telecom professional's toolkit. Now with a V-Bar and Sure-Set swivel feet, this tough-as-nails, award-winning ladder is the ultimate combination climbing tool.

1-YEAR LIMITED WARRANTY

Part #	Model	Stepladder Highest Standing Level	Stepladder Max Reach*	Extension Highest Standing Level	Extension Max Reach*	Spread	Storage Width at Base	Storage Depth	Weight
13906-074	6	3' 9"	10' 3"	6' 7"	13' 1"	3' 8"	2' 1"	7"	23 lbs
13908-074	8	5' 8"	12' 2"	10' 4"	17' 2"	4' 11"	2' 4"	7"	31 lbs

*A 5' 6" person with a 12" vertical reach