

4', 5', 6', & 8' STEPLADDER LIGHTWEIGHT WITH SLIM PROFILE STRONGER THAN MOST STANDARD A-FRAMES

1. COMFORTABLE STANDING PLATFORM

Extra-wide 3" steps with treads reduce slipping and foot fatigue. At 165 square inches, the comfortable standing platform creates a sturdy workspace that fully supports the feet. Work in comfort for extended periods.

2. INNOVATIVE TOP CAP


The MightyLite's innovative top cap features hooks, port holes, slots and grooves to keep your materials within reach while working.

3. NON-CONDUCTIVE, HI-VIZ GREEN FIBERGLASS

Our Hi-Viz green fiberglass is lightweight and non-conductive. The vibrant green color is proven to increase visibility, helping prevent injuries from people or objects bumping the ladder while in use.

4. GROUND CUE[®]

Up to 20% of all ladder injuries happen from missing the bottom step while descending the ladder. Ground Cue makes an audible and tactile "click" that alerts you when you've reached the bottom step of the ladder.




 NON-CONDUCTIVE FIBERGLASS
FIBRA DE VIDRIO NO CONDUCTORA






Lightweight, Non-conductive Fiberglass



One-Handed Closing Handle



Comfortable Standing Platform



Extra-Wide Non-Slip Feet



Innovative Top Cap and Tool Tray



Ground Cue® Available On IAA models



Feels Like Standing On The Ground

PRODUCT DESCRIPTION

The MightyLite™ 2.0 from Little Giant Ladder Systems is a sturdy, easy-to-use stepladder that is built to last. This lightweight ladder was engineered with a slim storage profile, while still supporting an impressive weight capacity. It's a "get stuff done" ladder built for pros. The MightyLite is available as a Type IA and Type IAA, rated to hold 300 or 375 lbs. Type IAA features Ground Cue.

1-YEAR LIMITED WARRANTY

Part #	Model	Rating	Stepladder Highest Standing Level	Stepladder Max Reach*	Spread	Step Depth	Storage Height	Storage Width	Storage Depth	Weight	
	15394-001	4' (2 step)	IA	1' 9.5"	8' 3.5"	2' 1.5"	3"	4' 3"	1' 8.25"	5"	13.5 lbs
EA905ED-2A	15404-001	4' (2 step)	IAA	1' 9.5"	8' 3.5"	2' 1.5"	3"	4' 3"	1' 8.25"	5"	15.5 lbs
	15395-001	5' (3 step)	IA	2' 8.5"	9' 2.5"	2' 8"	3"	5' 2.5"	1' 9.5"	5"	16.5 lbs
EA905ED-3A	15405-001	5' (3 step)	IAA	2' 8.5"	9' 2.5"	2' 8"	3"	5' 2.5"	1' 9.5"	5"	19 lbs
	15396-001	6' (4 step)	IA	3' 7.5"	10' 1.75"	3' 2"	3"	6' 3.5"	1' 10.75"	5"	19.5 lbs
EA905ED-4A	15406-001	6' (4 step)	IAA	3' 7.5"	10' 1.75"	3' 2"	3"	6' 3.5"	1' 10.75"	5"	22.5 lbs
	15398-001	8' (6 step)	IA	5' 6.25"	12' .25"	4' 3"	3"	8' 3"	2' 1.25"	5"	26 lbs
EA905ED-6A	15408-001	8' (6 step)	IAA	5' 6.25"	12' .25"	4' 3"	3"	8' 3"	2' 1.25"	5"	30 lbs

*A 5' 6" person with a 12" vertical reach