

# EA911AG-13~-15、-33~-35、-53~-55



品番	厚さ	長さ	重量	硬度	引張切断強さ kgf		伸び率 %		直角形引裂強さ kgf		耐寒温度 ℃
					縦	横	縦	横	縦	横	
<del>廃番</del> EA911AG-13	<del>0.3mm</del>	<del>2m</del>	<del>0.9kg</del>	<del>#400</del>	<del>7.2</del>	<del>6.4</del>	<del>270</del>	<del>280</del>	<del>2.37</del>	<del>2.33</del>	<del>25</del>
<del>廃番</del> EA911AG-14	<del>0.3mm</del>	<del>5m</del>	<del>2.25kg</del>	<del>#400</del>	<del>7.2</del>	<del>6.4</del>	<del>270</del>	<del>280</del>	<del>2.37</del>	<del>2.33</del>	<del>25</del>
EA911AG-15	0.3mm	10m	4.5kg	#400	7.2	6.4	270	280	2.37	2.33	-25
<del>廃番</del> EA911AG-33	<del>0.5mm</del>	<del>2m</del>	<del>1.32kg</del>	<del>#400</del>	<del>12.3</del>	<del>11</del>	<del>290</del>	<del>290</del>	<del>2.79</del>	<del>2.73</del>	<del>40</del>
<del>廃番</del> EA911AG-34	<del>0.5mm</del>	<del>5m</del>	<del>3.3kg</del>	<del>#400</del>	<del>12.3</del>	<del>11</del>	<del>290</del>	<del>290</del>	<del>2.79</del>	<del>2.73</del>	<del>40</del>
EA911AG-35	0.5mm	10m	6.6kg	#400	12.3	11	290	290	2.79	2.73	-40
<del>廃番</del> EA911AG-53	<del>0.8mm</del>	<del>2m</del>	<del>2.08kg</del>	<del>#480</del>	<del>22.6</del>	<del>21.7</del>	<del>340</del>	<del>400</del>	<del>6.87</del>	<del>7.2</del>	<del>40</del>
<del>廃番</del> EA911AG-54	<del>0.8mm</del>	<del>5m</del>	<del>5.2kg</del>	<del>#480</del>	<del>22.6</del>	<del>21.7</del>	<del>340</del>	<del>400</del>	<del>6.87</del>	<del>7.2</del>	<del>40</del>
<del>廃番</del> EA911AG-55	<del>0.8mm</del>	<del>10m</del>	<del>10.4kg</del>	<del>#480</del>	<del>22.6</del>	<del>21.7</del>	<del>340</del>	<del>400</del>	<del>6.87</del>	<del>7.2</del>	<del>40</del>

○値は実測値です。保証値ではありません。

- 材質…PVC
- 色…透明
- 幅…915mm