

赤色  
(危険シール付)



WB-2R



WB-1R



危険シール付

〈屋根付〉



WB-4AR



WB-3AR  
EA940CS-322



WB-2AR  
EA940CS-321



WB-1AR



WB-13AR  
EA940CS-324



WB-12AR  
EA940CS-323

赤色〈危険シール付〉

EA940CS-321

EA940CS-322

EA940CS-323

EA940CS-324

種類	品番	取付スペース	ボックス外形寸法(mm) (幅・高さ・奥行)			木板寸法(mm)			有効 フカサ	バンド 通し穴	
		ELB	タテ	ヨコ	フカサ	タテ	ヨコ	板厚			
屋根付	タテ型	WB-1AR	3P 30AF×1	256	160	130	170	100	15	90	有
		WB-2AR	3P 60AF×1	295	196	150	200	120	15	100	有
		WB-3AR	3P100AF×1	377	235	180	260	150	15	120	有
		WB-4AR	3P100AF×1	430	265	195	300	180	15	140	有
屋根付	ヨコ型	WB-12AR	3P 60AF×2	280	332	150	190	250	15	106	有
		WB-13AR	3P 60AF×3	335	384	195	210	300	15	140	有