



(A). Wire Pin Assignment and Wire Description.

CN. 1	Signal Assignment	CN. 2	WIRE COLOR
2	TMDS Data2 Shield	1	DRAIN
1	TMDS Data2+	2	ORANGE
3	TMDS Data2-	3	WHITE
5	TMDS Data1 Shield	4	DRAIN
4	TMDS Data1+	5	GREEN
6	TMDS Data1-	6	WHITE
8	TMDS Data0 Shield	7	DRAIN
7	TMDS Data0+	8	BROWN
9	TMDS Data0-	9	WHITE
11	TMDS Clock Shield	10	DRAIN
10	TMDS Clock+	11	BLUE
12	TMDS Clock-	12	WHITE
17	DDC/CEC Ground/HEAC Shield	13	DRAIN
14	Utility/HEAC+	17	YELLOW
19	Hot Plug Detect/HEAC-	19	WHITE
13	CEC	14	RED
15	SCL	15	VIOLET
16	SDA	16	BLUE
18	+5V Power	18	GREEN
SHELL		SHELL	BRAID

型番	L(約)
DH-HD14EM07BK	0.7m
DH-HD14EM10BK	1.0m
DH-HD14EM15BK	1.5m
DH-HD14EM20BK	2.0m
DH-HD14EM30BK	3.0m

EA940PM-11

EA940PM-12

EA940PM-13

仕様
対応機種

HDMI(タイプA・19ピン)側: HDMI入力端子を持つ液晶テレビ、プラズマテレビ、プロジェクター等、
HDMI(タイプC・19ピン)側: ビデオカメラレコーダーなどHDMI-Mini出力端子を持つ機器

規格
コネクター形状
ケーブルタイプ
伝送速度
対応解像度
シールド方法
プラグメッキ仕様
カラー

HDMI (High Speed HDMI Cable with Ethernet)認証
HDMI(タイプA・19ピン) - HDMIミニ(タイプC・19ピン)
ノーマルタイプ
10.2Gbps
4K × 2K対応
3重シールド
金メッキ
ブラック

製品改良の為、予告なく仕様の変更を行うことがあります。

本製品は、一般家庭、オフィスでの使用を想定しております。環境が著しく変化する場所、振動、ほこり、水濡れ等が起きる場所ではお使いできません。

Title:	外観図・仕様
Type:	DH-HD14EMBKシリーズ
SPNo.	
エレコム株式会社	