



品番	適合直径 (mm) D		L1 (mm)	L2 (mm)
	最小	最大		
EA947FE-1	3.2	4.8	19.9	11.6
EA947FE-2	4.8	6.4	20.7	12.4
EA947FE-3	6.4	7.9	21.5	13.2
EA947FE-4	7.9	9.5	22.3	14.0
EA947FE-5	9.5	11.1	23.1	14.8
EA947FE-6	11.1	12.7	24.1	15.8
EA947FE-7	12.7	14.3	24.9	16.6
EA947FE-8	14.3	15.9	25.7	17.4
EA947FE-9	15.9	17.5	26.5	18.2
EA947FE-10	17.5	19.0	27.3	19.0
EA947FE-11	19.0	20.6	28.0	19.7
EA947FE-12	20.6	22.2	28.8	20.5
EA947FE-13	22.2	23.8	29.6	21.3
EA947FE-14	23.8	25.4	30.4	21.1
EA947FE-15	25.4	27.0	31.4	23.1
EA947FE-16	27.0	28.6	32.2	23.9
EA947FE-17	28.6	30.2	33.0	24.7
EA947FE-18	30.2	31.8	33.8	25.5
EA947FE-19	31.8	33.3	34.6	26.3