

EA948AU-1~9 (メスネジディンプルノブ)

材質…ナイロン 6  
メスネジ S45C(酸化クロメート処理)

| 品番                   | サイズ(mm)      |              |               |               |              |                |               | 質量(g)         |
|----------------------|--------------|--------------|---------------|---------------|--------------|----------------|---------------|---------------|
|                      | M            | Lf           | D             | H             | s            | e              | d             |               |
| EA948AU-1            | 3            | 5            | 16            | 11            | 2            | 0.3            | 11            | 4             |
| <del>EA948AU-2</del> | <del>4</del> | <del>5</del> | <del>16</del> | <del>11</del> | <del>2</del> | <del>0.3</del> | <del>11</del> | <del>4</del>  |
| EA948AU-3            | 5            | 5            | 16            | 11            | 2            | 0.3            | 11            | 3             |
| <del>EA948AU-4</del> | <del>5</del> | <del>6</del> | <del>20</del> | <del>14</del> | <del>4</del> | <del>0.3</del> | <del>15</del> | <del>6</del>  |
| <del>EA948AU-5</del> | <del>6</del> | <del>6</del> | <del>20</del> | <del>14</del> | <del>4</del> | <del>0.3</del> | <del>15</del> | <del>6</del>  |
| EA948AU-6            | 5            | 9            | 25            | 18            | 6            | 0.3            | 19            | 10            |
| <del>EA948AU-7</del> | <del>6</del> | <del>9</del> | <del>25</del> | <del>18</del> | <del>6</del> | <del>0.3</del> | <del>19</del> | <del>10</del> |
| <del>EA948AU-8</del> | <del>6</del> | <del>8</del> | <del>32</del> | <del>18</del> | <del>6</del> | <del>0.3</del> | <del>24</del> | <del>15</del> |
| <del>EA948AU-9</del> | <del>8</del> | <del>8</del> | <del>32</del> | <del>18</del> | <del>6</del> | <del>0.3</del> | <del>24</del> | <del>15</del> |

廃番

廃番

廃番

廃番

廃番

廃番

