

EA948BC-21~EA948BC-25  
 (メスネジステンレス製ノブ)

材質…SUS303(バフ研磨)

	サイズ(mm)							質量 (g)
	M	Lf	D	H	s	A	d	
EA948BC-21	M4	9.5	16	9.5	6	2.5	8	7
EA948BC-22	M5	11.5	20	11.5	7.5	4	10	13
EA948BC-23	M6	15	24	15	10	5	12	23
<del>EA948BC-24</del>	<del>M8</del>	<del>18</del>	<del>30</del>	<del>18</del>	<del>12</del>	<del>6</del>	<del>16</del>	<del>45</del>
<del>EA948BC-25</del>	<del>M10</del>	<del>23</del>	<del>36</del>	<del>23</del>	<del>15</del>	<del>8</del>	<del>20</del>	<del>86</del>

廃番  
 廃番

(単位mm)

