

EA948BC-1~EA948BC-9A
 (オネジステンレス製ノブ)

材質…SUS303(バフ研磨)

	サイズ(mm)							質量 (g)
	M	Lm	D	H	s	A	d	
EA948BC-1	M4	6	16	9.5	6	2.5	8	9
EA948BC-2A	M4	10	16	9.5	6	2.5	8	10
EA948BC-3A	M4	16	16	9.5	6	2.5	8	10
EA948BC-4A	M5	10	20	11.5	7.5	4	10	15
EA948BC-5A	M5	16	20	11.5	7.5	4	10	16
EA948BC-6A	M5	20	20	11.5	7.5	4	10	16
EA948BC-7A	M6	16	24	15	10	5	12	28
EA948BC-8A	M6	20	24	15	10	5	12	30
EA948BC-9A	M6	25	24	15	10	5	12	32

