

**EA948BJ-11~13**

(メスネジステンレス取手)

材質 SUS303(バフ研磨)

	A	L <sub>1</sub>	L	M	L <sub>f</sub>	H	h	許容荷重(N)	適用座金	質量(g)
BJ-11	6	80	86	M4	10	30	24	1000	LY-10	26
BJ-12	10	10	110	M5	11	30	20	1000	LY-16A	82
BJ-13	10	120	130	M6	11	40	30	1000	LY-16	104

