

● 材質・仕上げ

 RoHS指令適合


SJN スティール製
M(並目): M3-M4

SJN スティール製
M(並目): M6-M20

SUM24L
四三酸化鉄皮膜(黒)

SUM22
四三酸化鉄皮膜(黒)

単位: mm

品番  1 スティール製	EA品番	M(並目)	L	Lf	B	質量(g)
SJN-M4	EA948EB-4	M4	33	14	7	8
SJN-M6	EA948EB-6	M6	43	19	10	20
SJN-M8	EA948EB-8	M8	55	25	13	45
SJN-M10	EA948EB-10	M10	67	31	17	95
SJN-M12	EA948EB-12	M12	81	38	19	130
SJN-M16	EA948EB-16	M16	95	45	24	260
SJN-M20	EA948EB-20	M20	105	50	30	390