

## Basic Data

### Description

Screw with large thin head, Phillips cross recess. Twin thread. TSC-31, 32, 33 fully threaded, TSC-BH part-threaded.

### Suitable for

Mounting of sheet metal to sheet metal. Works in most materials – metal studwork, cabinets, wood, plugs. Mounting with cross-point or power screwdriver.

### Advantages

- Hardened electroplated steel.
- Extra sharp-pointed screw with self-tapping thread.
- Penetrates 2x0.9 mm sheet metal without pilot drilling.
- Extra broad head, 11.2 mm – good function in thin and soft materials.
- Twin steep-pitch thread – fast and easy running.
- No. 2 Phillips – ordinary screwdrivers and bits can be used.
- Fully threaded (except TSC-BH45, 65, 85 and 100) – works well in thin materials.
- Works in most materials – sheet metal studwork, cabinets, wood, plugs.
- Boxes of 100 – easy to handle (TSH-BH85 and 100 = boxes of 50).

### Material

Hardened electroplated steel. TSC-BH45, BH65, BH85 and BH100 are also yellow-chromated.

### Packaging

Cardboard carton.



| Range   | Type      | Ø x L<br>mm | Qty/Pack | Art. No.           |
|---|-----------|-------------|----------|--------------------|
|  | TSC-31    | 4.2 x 13    | 100      | 3782 010 EA949AA-1 |
|   | TSC-32    | 4.2 x 25    | 100      | 3782 020 EA949AA-2 |
|   | TSC-33    | 4.2 x 31    | 100      | 3782 030 EA949AA-3 |
|   | TSC-BH45  | 4.2 x 45    | 100      | 3782 040 EA949AA-4 |
|   | TSC-BH65  | 4.2 x 65    | 100      | 3782 050           |
|   | TSC-BH85  | 4.2 x 85    | 50       | 3782 060           |
|   | TSC-BH100 | 4.8 x 100   | 50       | 3782 070           |