

EA949DE-1~38 六角穴付ボルト

材 質：鉄

サイズ：

	ネジの 呼び径	ピッチ	全長	d k			k		s		t	入り数
				基準	最大	最小	基準	最小	基準	最小	最小	
EA949DE-1	M3	0.5	10	5.5	5.68	5.32	3	2.86	2.5	2.52	1.3	100
EA949DE-2	M3	0.5	12	5.5	5.68	5.32	3	2.86	2.5	2.52	1.3	100
EA949DE-3	M4	0.7	12	7	7.22	6.78	4	3.82	3	3.02	2	100
EA949DE-4	M4	0.7	15	7	7.22	6.78	4	3.82	3	3.02	2	90
EA949DE-5	M5	0.8	15	8.5	8.72	8.28	5	4.82	4	4.02	2.5	80
EA949DE-6	M5	0.8	20	8.5	8.72	8.28	5	4.82	4	4.02	2.5	75
EA949DE-7	M6	1	20	10	10.22	9.78	6	5.7	5	5.02	3	55
EA949DE-8	M6	1	25	10	10.22	9.78	6	5.7	5	5.02	3	50
EA949DE-9	M8	1.25	25	13	13.27	12.73	8	7.64	6	6.02	4	30
EA949DE-10	M8	1.25	30	13	13.27	12.73	8	7.64	6	6.02	4	25
EA949DE-11	M10	1.5	25	16	16.27	15.73	10	9.64	8	8.025	5	20
EA949DE-12	M10	1.5	30	16	16.27	15.73	10	9.64	8	8.025	5	10
EA949DE-13	M10	1.5	35	16	16.27	15.73	10	9.64	8	8.025	5	6
EA949DE-16	M12	1.75	25	18	18.27	17.73	12	11.57	10	10.025	6	6
EA949DE-17	M12	1.75	30	18	18.27	17.73	12	11.57	10	10.025	6	6
EA949DE-18	M12	1.75	35	18	18.27	17.73	12	11.57	10	10.025	6	6
EA949DE-26	M16	2	30	24	24.33	23.67	16	15.57	14	14.032	7	2
EA949DE-27	M16	2	35	24	24.33	23.67	16	15.57	14	14.032	7	2
EA949DE-28	M16	2	40	24	24.33	23.67	16	15.57	14	14.032	7	2
EA949DE-31	M20	2.5	30	30	30.33	29.67	20	19.48	17	17.05	10	2
EA949DE-32	M20	2.5	35	30	30.33	29.67	20	19.48	17	17.05	10	2
EA949DE-33	M20	2.5	40	30	30.33	29.67	20	19.48	17	17.05	10	2
EA949DE-36	M24	3	35	36	36.39	35.61	22	21.67	19	19.065	12	1
EA949DE-37	M24	3	40	36	36.39	35.61	22	21.67	19	19.065	12	1
EA949DE-38	M24	3	45	36	36.39	35.61	22	21.67	19	19.065	12	1

