



■寸法

(mm)

	呼び径	ピッチ	dk		da	ds		e	k		呼び	s		t
	(d)		Max	Min	Max	Max	Min	Min	Max	Min		Max	Min	Min
EA949DN-305~-330	M3	0.5	5.68	5.32	3.6	3.00	2.86	2.873	3.00	2.86	2.5	2.56	2.52	1.3
EA949DN-405~-430	M4	0.7	7.22	6.78	4.7	4.00	3.82	3.443	4.00	3.82	3	3.08	3.02	2.0
EA949DN-506~-550	M5	0.8	8.72	8.28	5.7	5.00	4.82	4.583	5.00	4.82	4	4.095	4.020	2.5
EA949DN-610~-650	M6	1.0	10.22	9.78	6.8	6.00	5.82	5.723	6.00	5.70	5	5.095	5.020	3.0
EA949DN-812~-870	M8	1.25	13.27	12.73	9.2	8.00	7.78	6.863	8.00	7.64	6	6.095	6.020	4.0
EA949DN-1016~-1100	M10	1.5	16.27	15.73	11.2	10.00	9.78	9.149	10.00	9.64	8	8.115	8.025	5.0
EA949DN-2020~-2120	M12	1.75	18.27	17.73	14.2	12.00	11.73	11.429	12.00	11.57	10	10.115	10.025	6.0
EA949DN-4030~-4150	M16	2.0	24.33	23.67	18.2	16.00	15.73	15.996	16.00	15.57	14	14.142	14.032	8.0