


図面／規格
【（＋）丸木ねじ】



呼び径	十字穴 の番号	d		dk		K		m 最大
		基準 寸法	許容差	基準 寸法	許容差	基準 寸法	許容差	
2.1	1	2.1	±0.07	3.9	±0.2	1.6	±0.1	2.5
2.4		2.4		4.4		1.8		2.7
2.7		2.7		5.0		2.0		2.9
3.1	2	3.1	±0.1	5.7	±0.25	2.3	±0.15	3.7
3.5		3.5		6.5		2.5		3.9
3.8		3.8		7.0		2.7		4.1
4.1		4.1		7.6		2.9		4.3
4.5		4.5		8.3		3.1		4.5
4.8	3	4.8	±0.12	8.9	±0.3	3.3	±0.2	4.7
5.1		5.1		9.4		3.5		5.9
5.5		5.5		10.2		3.8		6.1
5.8		5.8		10.7		4.0		6.3
6.2	4	6.2	±0.15	11.5	±0.35	4.2	±0.2	6.6
8.0		8.0		14.8		5.3		8.7