

EA949EW-41～53 タッピングビス(ステンレス)

材 質：ステンレス

サイズ：

サラネジ	呼び径	全長	ネジ 山数	十字穴		d		d k		k		入り数
				番号	m	最大	最小	基準	許容差	基準	許容差	
EA949EW-41	M 4	12	16	2	4.5	4.15	4	8.0	-0.5	2.3	0	90本
EA949EW-42		16										75
EA949EW-43		20										70
EA949EW-44		25										60
EA949EW-45		30										50
EA949EW-46		40										35
EA949EW-51	M 5	25	12	2	5.1	5.2	5	10.0	-0.6	2.8	0	35
EA949EW-52		30										30
EA949EW-53		40										25

* ねじの山数25.4mmに付

