

# EA949GC - 3 ~ 12 ナットパック

材 質：鉄・クロメートメッキ(SWCH8 ~ 10R)

サイズ：

	呼び径	ピッチ (並目)	m		s		e	dk/dw	入り数
			基準	許容差	基準	許容差			
EA949GC-3	M 3	0.5	2.4	0 -0.25	5.5	0 -0.2	6.4	5.3	300個
EA949GC-4	M 4	0.7	3.2	0 -0.3	7		8.1	6.8	230
EA949GC-5	M 5	0.8	4		8		9.2	7.8	180
EA949GC-6	M 6	1	5	0 -0.36	10	0 -0.25	11.5	9.8	160
EA949GC-8	M 8	1.25	6.5		13		15	12.5	80
EA949GC-10	M 1 0	1.5	8		17	19.6	16.5	40	
EA949GC-12	M 1 2	1.75	10	-0.36	19	0 -0.35	21.9	18	25

