

EA949HB-163~308 六角頭全ネジボルト

材 質：鉄、ユニクロメッキ

並目ねじ

サイズ

品番	ネジの 呼び径	ピッチ	全長	k		s		e	入り数
				基準	許容差	基準	許容差	約	
EA949HB-163	M16	2	50	10		24	0 -0.35	27.7	
EA949HB-164			60						
EA949HB-165			80						
EA949HB-166			100						
<del>EA949HB-183</del>	M18	2.5	<del>60</del>	12		27	0 0.35	31.2	
<del>EA949HB-184</del>			<del>80</del>						
<del>EA949HB-185</del>			<del>100</del>						
<del>EA949HB-186</del>			<del>130</del>						
<del>EA949HB-203</del>	M20	2.5	<del>60</del>	13	±0.2	30	0 0.35	34.6	
<del>EA949HB-204</del>			<del>80</del>						
<del>EA949HB-205</del>			<del>100</del>						
<del>EA949HB-206</del>			<del>120</del>						
<del>EA949HB-207</del>			140						5本
<del>EA949HB-222</del>	M22	2.5	<del>60</del>	14		32	0 0.4	37	
<del>EA949HB-223</del>			<del>80</del>						
<del>EA949HB-224</del>			<del>100</del>						
<del>EA949HB-225</del>			<del>140</del>						
<del>EA949HB-242</del>	M24	3	<del>60</del>	15		36	0 0.4	41.6	
<del>EA949HB-243</del>			<del>80</del>						
<del>EA949HB-244</del>			<del>100</del>						
<del>EA949HB-303</del>	M30	3.5	<del>60</del>	19	±0.25	46	0 0.4	53.1	
<del>EA949HB-304</del>			<del>80</del>						
<del>EA949HB-305</del>			<del>90</del>						
<del>EA949HB-306</del>			<del>100</del>						
<del>EA949HB-307</del>			<del>110</del>						
<del>EA949HB-308</del>	<del>120</del>								

183~308  
廃番

