

EA949HC-61~128 六角頭全ボルト

材 質：ステンレス

サイズ

	ネジの 呼び径	ピッチ	全長	k		s		e	入り数
				基準	許容差	基準	許容差	約	
EA949HC-61	M6	1	12	4	±0.15	10	0 -0.2	11.5	23
EA949HC-62			16						20
EA949HC-63			20						18
EA949HC-64			25						17
EA949HC-65			30						13
EA949HC-66			40						12
EA949HC-67			50						10
EA949HC-81	M8	1.25	16	5.5	±0.15	13	0 -0.25	15	20
EA949HC-82			20						18
EA949HC-83			25						16
EA949HC-84			30						15
EA949HC-85			40						12
EA949HC-86			50						10
EA949HC-101	M10	1.5	20	7	±0.2	17	0 -0.25	19.6	16
EA949HC-102			25						15
EA949HC-103			30						15
EA949HC-104			40						12
EA949HC-105			50						10
EA949HC-106			60						8
EA949HC-107			75						6
EA949HC-108			100						5
EA949HC-121	M12	1.75	25	8	±0.2	19	0 -0.35	21.9	12
EA949HC-122			30						11
EA949HC-123			40						9
EA949HC-124			50						7
EA949HC-125			60						7
EA949HC-126			75						5
EA949HC-127			90						4
EA949HC-128			100						4

