

〔焼入〕平ワッシャー(10枚)



品番	サイズ(mm)			重量(g)
	A	B	C	
EA949HM-111	10	6.4	3	1.5
EA949HM-114	13	8.4	3	2
EA949HM-115	16.3		3	3.5
EA949HM-116	23	10.5	4	10
EA949HM-117	16.3		3	3
EA949HM-118	19	13	3	4.5
EA949HM-119	28		4	16
EA949HM-120	19	17	3	4.5
EA949HM-121	25		4	11
EA949HM-122	35	21	5	35
EA949HM-123	25		4	6
EA949HM-124	31	21	5	21
EA949HM-125	45		6	60
EA949HM-126	31	21	5	14.5
EA949HM-127	38		5	29
EA949HM-128	50		6	77

RoHS指令適合品

- 材質  
本体: S45C、焼入焼戻、黒染め

●使用例、使用方法

