


図面／規格 【Uナット】



EA949SD-604 ~ -616

	呼び径	ピッチ	二面幅 (s)		全高 (h)		高さ (m)
			基準寸法	許容差	基準寸法	許容差	
	M3	0.5	5.5		3.2		2.7
-604	M4	0.7	7	0	3.8	± 0.3	3
-605	M5	0.8	8	-0.2	4.6		3.9
-606	M6	1	10		5.1		4.2
-608	M8	1.25	13	0	7.3	± 0.4	6.1
-610	M10	1.5	17	-0.25	8.3		7.1
-612	M12	1.75	19		10.5		9
-616	M14	2	22	0 -0.35	12.5	± 0.5	11
	M16	2	24		14.5		13
	M18	2.5	27		16		14
	M20	2.5	30		17.5		15.4
	M22	2.5	32	0	19.5	± 0.6	17.2
	M24	3	36	-0.4	21.5		18.8

呼び径	ピッチ	二面幅 (s)		全高 (h)		高さ (m)
		基準寸法	許容差	基準寸法	許容差	
M27	3	41	0 -0.4	24	± 0.6	21.2
M30	3.5	46		27	± 0.8	24
M33	3.5	50		29.5	± 0.8	26.5
M36	4	55	0 -0.45	32.5	± 1	29.5
M39	4	60		35		31.8
M42	4.5	65		38	± 1.5	34.5
M45	4.5	70	40	36		
M48	5	75	42	38		
M52	5	80	0 -0.55	46	± 2	42
M56	5.5	85		49		44.5
M60	5.5	90		52		47.5
M64	6	95	54		50	