


図面／規格
【六角穴付き丸ナット】



呼び径 d	B	b	L	D	C
M4	4	3	5 ⁰ _{-0.1}	φ8.5 ⁰ _{-0.1}	0.3
M5	5	4	7 ⁰ _{-0.1}	φ10 ⁰ _{-0.1}	0.3
M6	6	5	9 ⁰ _{-0.1}	φ13 ⁰ _{-0.1}	0.5
M8	8	6.5	12 ⁰ _{-0.1}	φ16 ⁰ _{-0.1}	0.5
M10	10	8	14 ⁰ _{-0.1}	φ18 ⁰ _{-0.1}	0.5