

品番	メトリック		UNC		UNF		BSW		BSF		CUMMINS HEAD BOLT	
	サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)
EA949VC-3A	M3	3.3	5-40	3.4			1/8-40	3.4				
EA949VC-4A	M4-0.7	4.3	8-32	4.4	8-36	4.4						
EA949VC-4.5A			10-24	5.1			3/16-24	5				
EA949VC-5A	M5-0.8	5.3	12-24	5.8	10-32	5.1			3/16-32	5		
EA949VC-6A	M6-1.0	6.3					1/4-20	6.7				
EA949VC-7A	M7-1.0	7.3	5/16-18	8.3								
EA949VC-8A	M8-1.0・1.25	8.3			5/16-24	8.2						
EA949VC-10A	M9-1.0/M10-1.5	9.3/10.3							3/8-20	9.8		
EA949VC-10BA	M10-1.0・1.25	10.3			3/8-24	9.8						
EA949VC-11A	M11-1.0・1.25・1.5	11.3			7/16-20	11.5			7/16-18	11.5		
EA949VC-12A	M12・M13全ピッチ	12.3・13.3					1/2-12	13	1/2-16	13		
EA949VC-14A	M14-1.5・2.0/M15	14.3/15.3							9/16-16	14.5		
EA949VC-16A	M16-1.5・2.0	16.3	5/8-11	16.5							11/16-16	18
EA949VG-1A			8-32	4.4								
EA949VG-2A			10-24	5.1								
EA949VG-3A			12-24	5.8								
EA949VG-4A			1/4-20	6.7								
EA949VG-5A			5/16-18	8.3								
EA949VG-6A			3/8-16	9.9								
EA949VG-7A			7/16-14	11.5								
EA949VG-8A			1/2-13	13								
EA949VG-9A			5/8-11	16.5								
EA949VH-1A					8-36	4.4						
EA949VH-2A					10-32	5.1						
EA949VH-3A					12-28	5.8						
EA949VH-4A					1/4-28	6.6						
EA949VH-5A					5/16-24	8.2						
EA949VH-6A					3/8-24	9.8						
EA949VH-7A					7/16-20	11.5						
EA949VH-8A					1/2-20	13						
EA949VH-9A					5/8-18	16.3						
EA949VG-11			8-32	4.4								
EA949VG-12			10-24	5.1								
EA949VG-13			12-24	5.8								
EA949VG-14			1/4-20	6.7								
EA949VG-15			5/16-18	8.3								
EA949VG-16			3/8-16	9.9								
EA949VG-17			7/16-14	11.5								
EA949VG-18			1/2-13	13								
EA949VG-19			5/8-13	16.5								
EA949VH-11					8-36	4.4						
EA949VH-12					10-32	5.1						
EA949VH-13					12-28	5.8						
EA949VH-14					1/4-28	6.6						
EA949VH-15					5/16-24	8.2						
EA949VH-16					3/8-24	9.8						
EA949VH-17					7/16-20	11.5						
EA949VH-18					1/2-20	13						
EA949VH-19					5/8-18	16.3						