

EA952S-41～EA952S-402 [押しスプリング (1m)]

仕様:

| 品番 | 外径 (mm) | 線径 (mm) | ピッチ (mm) | 許容荷重 (kgf) |
|------------|------------|------------|-------------|---------------|
| EA952S-41 | 4 | 0.5 | 2.0 | 0.5 |
| EA952S-51 | 5 | 0.5 | 2.0 | 0.4 |
| EA952S-52 | 5 | 0.8 | 2.3 | 0.4 |
| EA952S-61 | 6 | 0.5 | 2.0 | 0.3 |
| EA952S-62 | 6 | 1.0 | 2.5 | 2.6 |
| EA952S-71 | 7 | 0.5 | 2.5 | 0.3 |
| EA952S-72 | 7 | 1.4 | 3.4 | 6.0 |
| EA952S-81 | 8 | 1.0 | 3.0 | 2.0 |
| EA952S-101 | 10 | 1.0 | 4.0 | 1.6 |
| EA952S-102 | 10 | 1.6 | 4.6 | 6.6 |
| EA952S-103 | 10 | 2.0 | 4.5 | 12.7 |
| EA952S-104 | 10 | 2.6 | 5.1 | 26.5 |
| EA952S-111 | 11 | 1.6 | 4.6 | 5.9 |
| EA952S-121 | 12 | 1.0 | 4.5 | 1.4 |
| EA952S-122 | 12 | 1.6 | 4.6 | 5.4 |
| EA952S-123 | 12 | 2.0 | 4.5 | 10.4 |
| EA952S-124 | 12 | 2.6 | 5.1 | 19.7 |
| EA952S-141 | 14 | 1.0 | 5.0 | 1.1 |
| EA952S-142 | 14 | 1.6 | 4.6 | 4.7 |
| EA952S-143 | 14 | 2.0 | 5.0 | 9.0 |
| EA952S-144 | 14 | 2.6 | 5.6 | 19.9 |
| EA952S-151 | 15 | 1.6 | 5.6 | 4.1 |

| 品番 | 外径 (mm) | 線径 (mm) | ピッチ (mm) | 許容荷重 (kgf) |
|------------|------------|------------|-------------|---------------|
| EA952S-161 | 16 | 1.0 | 5.0 | 1.0 |
| EA952S-162 | 16 | 1.6 | 6.6 | 4.1 |
| EA952S-163 | 16 | 2.0 | 7.0 | 8.2 |
| EA952S-164 | 16 | 2.6 | 6.6 | 16.6 |
| EA952S-165 | 16 | 3.0 | 6.0 | 26.4 |
| EA952S-171 | 17 | 1.6 | 5.6 | 3.9 |
| EA952S-181 | 18 | 2.0 | 7.0 | 7.3 |
| EA952S-182 | 18 | 2.6 | 7.6 | 15.7 |
| EA952S-183 | 18 | 3.0 | 6.5 | 21.9 |
| EA952S-191 | 19 | 2.0 | 6.0 | 6.5 |
| EA952S-201 | 20 | 2.0 | 6.0 | 6.6 |
| EA952S-202 | 20 | 2.6 | 6.6 | 13.8 |
| EA952S-203 | 20 | 3.0 | 7.0 | 21.3 |
| EA952S-204 | 20 | 3.5 | 6.5 | 33.7 |
| EA952S-205 | 20 | 4.0 | 8.0 | 50.0 |
| EA952S-221 | 22 | 2.0 | 6.5 | 5.9 |
| EA952S-222 | 22 | 2.6 | 6.6 | 12.6 |
| EA952S-223 | 22 | 3.0 | 7.0 | 19.0 |
| EA952S-224 | 22 | 3.5 | 8.5 | 30.5 |
| EA952S-225 | 22 | 4.0 | 8.0 | 44.7 |
| EA952S-231 | 23 | 3.5 | 7.5 | 29.3 |
| EA952S-241 | 24 | 2.0 | 7.0 | 5.4 |

廃番

| 品番 | 外径 (mm) | 線径 (mm) | ピッチ (mm) | 許容荷重 (kgf) |
|-----------------------|---------------|----------------|-----------------|-----------------|
| EA952S-242 | 24 | 2.6 | 7.6 | 11.7 |
| EA952S-243 | 24 | 3.0 | 7.0 | 27.7 |
| EA952S-244 | 24 | 3.5 | 7.5 | 41.3 |
| EA952S-245 | 24 | 4.0 | 8.0 | 41.5 |
| EA952S-261 | 26 | 2.0 | 6.5 | 5.0 |
| EA952S-262 | 26 | 3.0 | 7.0 | 16.4 |
| EA952S-263 | 26 | 3.5 | 8.5 | 26.3 |
| EA952S-264 | 26 | 4.0 | 9.0 | 37.9 |
| EA952S-281 | 28 | 3.5 | 8.5 | 24.4 |
| EA952S-282 | 28 | 4.0 | 10.0 | 36.1 |
| EA952S-301 | 30 | 3.5 | 9.5 | 22.9 |
| EA952S-302 | 30 | 4.0 | 9.0 | 33.8 |
| EA952S-303 | 30 | 5.0 | 10.0 | 64.9 |
| EA952S-321 | 32 | 4.0 | 9.0 | 31.8 |
| EA952S-341 | 34 | 4.0 | 9.0 | 30.0 |
| EA952S-351 | 35 | 3.5 | 9.5 | 19.6 |
| EA952S-361 | 36 | 4.0 | 9.0 | 28.2 |
| EA952S-362 | 36 | 5.0 | 10.0 | 55.0 |
| EA952S-381 | 38 | 4.0 | 9.0 | 26.7 |
| EA952S-382 | 38 | 5.0 | 10.0 | 51.7 |
| EA952S-401 | 40 | 4.0 | 9.0 | 25.2 |
| EA952S-402 | 40 | 5.0 | 11.0 | 49.5 |

●材質…バネ鋼

●長さ…1m

※許容荷重は1mの長さで使用された場合の数値です。