

EA952VB - 4 ~ VV - 77 押しスプリング(ステンレス : SUS304)

仕 様 :

	外径 mm	線 径 mm	自由高さ mm	許容荷重 時高さmm	許容荷重		密着高さ mm	総巻数	ばね定数		入 数	ピッチ mm
					N	kgf			N・mm	kgf/mm		
EA952VB-4	2.5	0.23	4.0	2.00	1.34	0.137	1.5	5.5	0.67	0.0684	20	1.0
EA952VC-7	3	0.32	7.0	3.70	2.93	0.299	2.88	8.0	0.89	0.0908	20	1.0
EA952VC-9	3	0.29	9.0	4.24	2.21	0.226	3.05	9.5	0.46	0.0474	20	1.1
EA952VC-9.5	3	0.35	9.5	5.26	3.72	0.38	4.2	11.0	0.39	0.0396	20	1.0
EA952VD-10	3.5	0.4	10.0	5.52	4.69	0.479	4.4	10.0	1.05	0.107	20	1.1
EA952VE-11	4	0.5	11.0	6.60	7.10	0.724	5.75	10.5	1.69	0.172	20	1.2
EA952VE-12	4	0.45	12.0	6.36	5.97	0.609	4.95	10.5	1.06	0.108	20	1.3
EA952VF-12	4.5	0.55	12.0	6.80	8.93	0.911	5.5	10.5	1.72	0.175	20	1.3
EA952VG-13	5	0.7	13.0	8.48	14.90	1.52	7.35	11.0	3.29	0.336	20	1.3
EA952VH-16	6	0.8	16.0	9.92	19.31	1.97	8.4	11.0	3.18	0.324	20	1.6
EA952VJ-17	6.5	0.9	17.0	10.96	24.60	2.51	9.45	11.0	4.07	0.415	20	1.7
EA952VK-18	7	1	18.0	12.00	29.79	3.04	10.5	11.0	5.04	0.514	20	1.8
EA952VL-22	8	1.2	22.0	14.96	47.82	4.88	13.2	11.5	6.80	0.694	10	2.0
EA952VM-25	9	1.4	25.0	17.88	61.05	6.23	16.1	12.0	8.58	0.875	10	2.2
EA952VN-28	10	1.6	28.0	20.32	83.50	8.52	18.4	12.0	10.88	1.11	6	2.4
EA952VP-31	11	1.8	31.0	22.76	108.78	11.1	20.7	12.0	13.23	1.35	6	2.7
EA952VQ-34	12	2	34.0	25.20	138.18	14.1	23	12.0	15.68	1.60	6	3.0
EA952VR-40	13	2.3	40.0	31.00	183.26	18.7	28.8	13.0	20.38	2.08	5	3.2
EA952VS-42	15	2.6	42.0	32.32	227.36	23.2	29.9	12.0	23.52	2.40	3	3.6
EA952VT-45	16	2.9	45.0	35.72	286.16	29.2	33.4	12.0	30.87	3.15	2	3.9
EA952VU-52	17	3.2	52.0	42.40	341.04	34.8	40	13.0	35.57	3.63	2	4.1
EA952VV-77	20	2.9	77.0	51.40	231.28	23.6	45	16.0	9.90	1.01	2	5.0