

# EA966CA-31~-58

(ステンレス製セットカラー)



★ 特 長

- 現場で位置調整したい時や、シャフトへの溝調加工が困難な時などに便利です。
- 片側は30° 面取りをしてベアリング外輪との緩衝を避けました。

■ 材 質 … ステンレス(SUS304)

品番	内径 φ B H8	幅 L±0.1	面取径 φ D 1	外径 φ D±0.1	トメジ M
EA966CA-31	4	6	*	12	☆M4X4
EA966CA-32	4	8	*	12	☆M4X4
EA966CA-33	5	6	*	14	☆M4X4
EA966CA-34	5	8	*	14	☆M4X4
EA966CA-35	6	8	*	15	☆M4X4
EA966CA-36	6	10	*	16	☆M4X4
EA966CA-37	8	8	13	16	☆M4X4
EA966CA-38	8	10	*	18	M4X4
EA966CA-39	10	8	16	18	M4X4
EA966CA-40	10	10	*	20	M4X4
EA966CA-41	12	8	20	22	M4X4
EA966CA-42	12	10	*	26	M5X6
EA966CA-43	13	10	*	26	M5X6
EA966CA-44	15	10	24	25	M4X4
EA966CA-45	15	12	*	28	M5X6
EA966CA-46	16	10	24	28	M5X6
EA966CA-47	16	12	*	28	M5X6
EA966CA-48	17	10	26	30	M6X6
EA966CA-49	20	12	29	32	M6X6
EA966CA-50	20	15	*	32	M6X6
EA966CA-51	25	15	37	38	M6X6
EA966CA-52	25	18	*	42	M8X8
EA966CA-53	30	16	42	45	M8X8
EA966CA-54	30	20	*	49	M8X8
EA966CA-55	35	20	*	59	M8X8
EA966CA-56	40	22	*	72	M10X12
EA966CA-57	45	22	*	75	M10X12
EA966CA-58	50	25	*	79	M10X12

(単位 mm)

☆印はネジ1本

