

## EA966CB-1~-22

(スチール製スリットカラー)

黒染めタイプ

## 特長

- ・シャフトに傷をつける事なく固定ができます。
- ・スライドシャフトや頻繁に取付け位置を変更する所に最適です。

	内径 $\phi B_{H8}$	外径 $\phi D_{\pm 0.1}$	幅 $L_{\pm 0.1}$	$\phi d$	R	W	X	Y	A	トメジ M	六角穴付 ボルト
CB-1	3	15	8	3.4	3	1	4.5	3	4.5	M3XP0.5	M3X8
CB-2	4	15	8	3.4	3	1	4.5	3	4.5	M3XP0.5	M3X8
CB-3	5	20	10	4.5	3.75	1	6	4	6	M4XP0.7	M4X10
CB-4	6	20	10	4.5	3.75	1	6	4	6	M4XP0.7	M4X10
CB-5	8	25	8	3.4	3	1.5	8	5	7	M3XP0.5	M3X10
CB-6	8	25	10	4.5	3.75	1.5	8	5	9	M4XP0.7	M4X12
CB-7	10	30	10	4.5	3.75	1.5	9	5	11	M4XP0.7	M4X12
CB-8	12	30	10	4.5	3.75	1.5	10	5	11	M4XP0.7	M4X12
CB-9	12	30	12	5.5	4.5	1.5	10	5	11	M5XP0.8	M5X16
CB-10	13	30	10	4.5	3.75	1.5	10	5	11	M4XP0.7	M4X12
CB-11	15	35	12	5.5	4.5	1.5	12	6	13	M5XP0.8	M5X16
CB-12	16	35	10	4.5	3.75	1.5	12	6	13	M4XP0.7	M4X12
CB-13	16	35	12	5.5	4.5	1.5	12	6	13	M5XP0.8	M5X16
CB-14	20	40	10	4.5	3.75	1.5	14	7	15	M4XP0.7	M4X16
CB-15	20	40	12	5.5	4.5	1.5	14	7	15	M5XP0.8	M5X16
CB-16	25	45	12	5.5	4.5	1.5	17	7	18	M5XP0.8	M5X16
CB-17	25	50	15	7	6	1.5	18	10	18	M6XP1.0	M6X25
CB-18	30	55	15	7	6	1.5	20	10	—	M6XP1.0	M6X25
CB-19	35	60	15	7	6	2	23	12	—	M6XP1.0	M6X25
CB-20	40	70	18	9	7	2	26	13	—	M8XP1.25	M8X30
CB-21	45	75	18	9	7	3	28	14	—	M8XP1.25	M8X30
CB-22	50	85	22	11	9	3	32	16	—	M10XP1.5	M10X35

(単位 mm)

